



PRIMUS® IS THE PAST, PRESENT AND FUTURE OF HEALTHCARE LAUNDRY

Primus® has the heritage and innovation to deliver exceptional results

Since 1911, Primus® has innovated to bring its customers and their customers premium laundry results. Over the last 100 years, this constant innovation has positioned Primus® as the industry leader. Exceptional levels of hygiene and service characterize the brand and industry development, particularly in the field of healthcare laundry solutions. Nowadays, Primus® machines are a beacon of efficiency and outstanding hygiene to ensure user satisfaction. The patented technology developed by Primus® for the healthcare industry, such as Optiload® and Trace-Tech®, provides exquisite performance while being user-friendly, and facilitating easy control, monitoring and analysis.





A SOLID FOUNDATION FOR YOUR LAUNDRY HYGIENE

IMPLEMENTING THE PRIMCARE SOLUTION WILL ENSURE YOUR LAUNDRY OPERATIONS CONFORM TO BEST HYGIENE PRACTICES

- Where HACCP (Hazard Analysis and Critical Control Points) control measurement is the requirement for the food industry, RABC (Risk Analysis and Biocontamination Control) is the guideline for the laundry industry. Both control systems will help you to increase the level of hygiene in your hospital or nursing home.
- A physical wall separates the laundry into two areas: soiled area and clean area.
- No risk of contact or crossing between soiled and clean linen.

- As an option, separate atmospheric pressures can be created between clean and soiled areas to further reduce the risk of clean linen being soiled by dirty linen.
- Specific high-temperature hygiene wash programme to clean the laundry.
- Offers the best **solution** to keep your linen clean.
- Gives your laundry flexibility to adapt to any changes in regulations.





PRIMUS® WILL BE YOUR PARTNER THROUGHOUT THE ENTIRE PROCESS

PRIMUS® PROVIDES YOU WITH A TOTAL SOLUTION

COLLECTING AND SORTING

Presorting of laundry is carried out by collection staff and the different wash loads are separated into wash types by staff wearing protective gloves.

STORAGE

Linen should be stored no longer than 48 hours, and trolleys should be cleaned before each use. A dedicated room with a lower air pressure, washing station, and floor U-bend also is required.

WASHING

Wash loads of the same type are processed together to avoid crossing dirty and clean laundry. The Primus® Trace-tech® system controls temperature, mechanics, time and chemicals in order to ensure ensures the optimal wash quality.

FINISHING

Handling of clean laundry is carried out by staff who have used hand disinfection. Gloves should be worn to avoid clean laundry being soiled.

CLEAN STORAGE

Clean laundry should be stored directly after processing and covered with plastic film in closed cabinets. The room and the trolleys should be cleaned regularly and separate flows between clean and soiled linen must be respected.






PRIMUS® WILL GUIDE YOU IN YOUR PROJECT

Our team of specialist advisers, experienced designers and Primus® certified partners are ready to assist you in designing a solution that meets your specific requirements, including:

- An audit of your laundry
- A definition of needs
- A technical drawing with energy reservations
- Installation and maintenance of machines
- Training of technical staff and users






www.primuslaundry.com



PREMIUM CARE AND HYGIENE USING THE INNOVA BARRIER SOLUTION







GoldenLock





THE PRIMUS® TOOLS THAT GIVE YOU MORE CONTROL



EASY AND UNLIMITED PROGRAMMING

The innovative XControl programmer brings laundry professionals unlimited programming possibilities. New washing programmes can be uploaded quickly and easily thanks to the handy USB plug.



SAFE AND USER-FRIENDLY LOCK

Fase of use, safety and ergonomics at your fingertips. The patented Golden Lock system will help you to easily open the machine before and after the wash cycle. Because the machine will not run until the door is securely locked, safety is ensured.

CONTROL YOUR COSTS

Optiload® calculates the weight of the load while you load the washer-extractor, and automatically adapts the amount of water, energy and detergent the machine will use. This will help you to spend less on energy and water costs and the productivity of your laundry facility will increase, also reducing your operating costs. Win-win!





WASH PROGRAMME COPY & EDIT

TRace-Tech

FULL QUALITY CONTROL

All washers are equipped with the revolutionary Primus® Trace-Tech® management software. A track-and-trace system that complies with RABC hygienic standards, it allows full quality control by providing records and statistics for each wash load. All data is stored and can be retrieved for creating operations reports.

Parameters **are continually controlled and stored** to bring you a detailed report of the washing process. This enables you to allow you to **check the accuracy** of the programme used.

The machines are equipped with water meters, live temperature measurement, an automatic weighing system and a water drainage tap to enable you to check the entire process.

MACHINE SET-UP

MONITORING




TRACEABILITY

TATISTICS & REPORT CREATION

LOCATION MANAGEMENT

SALES OVERVIEW





THE RIGHT EQUIPMENT FOR YOUR CARE FACILITY PRIMCARE SOLUTIONS

Primus® has developed a full range of machines to **simplify and optimise your laundry process**. With our full range of washer-extractors, combined with our innovative barrier machines, ranging from 18 kg to 180 kg, we have equipment to meet the needs of any care facility. Primus® offers you the **most comprehensive package of equipment and services in the industry**, and has now created a full solution - the **Primcare Solution**.























1 PRIMCARE ENTRY PACK

FOR A GOOD LAUNDRY PRACTICE FOUNDATION

Improve the quality of your linen and save time and costs with the Primcare Entry Pack. This solution enables you to **streamline the laundry process**. Your staff will be able to **save time** because the logistical process is very short: the laundry is just

around the corner. No more worries about linen stocks: your staff always has the right stock at their disposal. Moreover, you have the possibility to influence the entire process and benefit from the lowest cycle cost.







2 PRIMCARE HYGIENE CONTROL PACK

FOR TOTAL SAFETY

The Primcare Hygiene Control Pack ensures you stay on top of the laundry process. This solution focuses on **ultimate safety for patients**, **and staff** handling linen. Thanks to the innovative barrier

concept, it is almost impossible to mix clean and dirty linen thus ensuring an exceptional level of hygiene for your linen. Train your staff on how to achieve the best possible result and **increase your laundry throughput** by making best use of our innovative machine features, all while improving the quality of your linen.









3 PRIMCARE ULTIMATE CONTROL PACK

FOR ULTIMATE CONTROL

Follow every detail of the entire laundry process with the Primcare Ultimate Control Pack. **Monitoring and reporting** features track all steps

in the process, from washing, to drying and ironing. This actionable data enables you to optimize your laundry for maximum efficiency and profitability.











WORLDWIDE HEADQUARTERS

Alliance Laundry Systems P.O. Box 990 Shepard Street Ripon, WI 54971, USA Phone: +1 920 748 3121 Fax: +1 920 748 4564 alliancelaundry.com

FRANCE

Alliance Laundry France 3 rue Paul Rieupeyroux F-69800 Saint Priest, France Phone: +33 (0)4 78 79 55 75 Fax: +33 (0)4 72 04 62 72

ITALY

Alliance Laundry Italy SRL 73, Via Triumplina 25123 Brescia (BS), Italy Phone: +39 (0)30 2091006 Fax: +39 (0)30 2000239

SPAIN

Alliance Laundry Systems Spain C/ Solsones, 2 08820 – El Prat de Llobregat Barcelona, Spain Phone: +34 93 479 54 10 Fax: +34 93 379 18 76

CZECH REPUBLIC

Alliance Laundry CE Místecká 1116 Příbor, 742 58, Czech Republic Phone: +420 556 768 800 Fax: +420 556 768 882

BRASIL

Alliance Laundry Systems Brasil Edifício Office Design Berrini Avenida Luis Carlos Berrini, 1748 Sala 2106 São Paulo- SP, 04571-000, Brasil Phone: 55 + 11 5 508 - 2900

CHINA

Alliance Laundry Machinery Commercial And Trading Shanghai Co., Ltd. Room 101 A,1st Floor, No.1 Building NO.888 Lane Tianlin Road Min Hang District, Shanghai, China Post code: 200233 Phone: +86 21 33375288 Fax: +86 21 64227933

VIETNAM

Alliance Laundry Vietnam Company Limited Shophouse No. SH04-03, 103 North-South Road Sala Urban Area, An Loi Dong Ward, District 2 Ho Chi Minh, VIETNAM Phone: +84 936 072 268

INDIA

Alliance Laundry Private Limited 4, Shagun Arcade Premises Co-op Society Gen AKV marg, Dindoshi Malad East, Mumbai 400097 Phone: +91 99875 85708

U.A.E

Alliance Laundry BVBA (Dubai Branch) The Curve Building Showroom GS-08 P.O. Box 393291 Al Quoz 3 Dubai, U.A.E. Phone: +971 4 347 413

Phone: +971 4 347 4136 Phone: +971 4 347 4137 Fax: +971 4 347 4180